



MASTER Plastic LEDbulbs

MAS LEDbulb DT 6-40W B22 A60 CL

MASTER LEDbulb range delivers a dimmable glow effect for a welcoming, warm atmosphere, making it ideal for general lighting applications in the hospitality industry. Its unique design radiates warm light in all directions, making it a true alternative to the incandescent lamp. It is particularly suitable for public areas such as lobbies, corridors, stairwells, where the light is always on. Compatible with existing fixtures with an E27 or a B22 holder and designed for retrofit replacement of incandescent bulbs, MASTER LEDbulb delivers huge energy savings and minimises maintenance cost without any compromise on light quality.

Warnings and Safety

- Operating temperature range is between -20° C and 45° C ambient
- Operating temperature range is between -20° C and 45° C ambient
- Only to apply in dry or damp locations and most of open fixtures with lamp-holders that offer sufficient space (10 mm free air space)
- Only to apply in dry or damp locations and most of open fixtures with lamp-holders that offer sufficient space (10 mm free air space)
- Not intended for use with emergency light fixtures or exit lights
- Not intended for use with emergency light fixtures or exit lights

Product data

General Information	
Cap-Base	B22 [B22]
Nominal lifetime	25,000 hour(s)
Switching Cycle	50,000
Lighting Technology	LED
EU RoHS compliant	Yes

Light Technical	
Color Code	822-827 [tunable warm white]
Luminous Flux	470 lm
Color Designation	Warm White (WW)
Luminous Efficacy (rated) (Nom)	78.00 lm/W
Color Consistency	<6
Color rendering index (CRI)	80

MASTER Plastic LEDbulbs

LLMF At End Of Nominal Lifetime (Nom)	70 %
---------------------------------------	------

Operating and Electrical

Line Frequency	50 to 60 Hz
Input Frequency	50 to 60 Hz
Power Consumption	6 W
Lamp Current (Nom)	37 mA
Wattage Equivalent	40 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	instant full light s
Power Factor (Fraction)	0.7
Voltage (Nom)	220-240 V

Temperature

T-Case Maximum (Nom)	85 °C
----------------------	-------

Controls and Dimming

Dimmable	Yes
----------	-----

Mechanical and Housing

Bulb Finish	Clear
-------------	-------

Bulb Shape	A60 [A 60mm]
------------	--------------



Approval and Application

Suitable For Accent Lighting	No
Energy Consumption kWh/1000 h	6 kWh
EyeComfort	Yes

Product Data

Order product name	MAS LEDbulb DT 6-40W B22 A60 CL
Full product name	MAS LEDbulb DT 6-40W B22 A60 CL
Full product code	871869648130100
Order code	929001150602
Material Nr. (12NC)	929001150602
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696481301
Numerator - Packs per outer box	10
EAN/UPC - Case	8718696481318

Dimensional drawing




Product	D	C
MAS LEDbulb DT 6-40W B22 A60 CL	60 mm	110 mm

Product
MAS LEDbulb DT 6-40W B22 A60 CL

MASTER Plastic LEDbulbs

Photometric data



Light Distribution Diagram - MAS LEDbulb DT 6-40W B22 A60 CL

Spectral Power Distribution Colour - MAS LEDbulb DT 6-40W B22 A60 CL

