

# Classic filament LEDbulbs

## CLA LEDBulb ND 4-40W A60 E27 827 CL

Featuring a classic heritage design, Classic filament LEDbulbs combine the familiar shapes of classic incandescent bulbs with the benefits of the long lasting LED technology. They deliver beautiful, decorative warm-white light while saving around 90% on energy costs compared with traditional light bulbs.

### Product data

General Information	
Cap-Base	E27 [E27]
Nominal lifetime	15,000 hour(s)
Switching Cycle	20,000
Lighting Technology	LED
EU RoHS compliant	Yes
Light Technical	
Color Code	827 [CCT of 2700K]
Luminous Flux	470 lm
Color Designation	Warm White (WW)
Correlated Color Temperature (Nom)	2700 K
Luminous Efficacy (rated) (Nom)	117.50 lm/W
Color Consistency	<6
Color rendering index (CRI)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Line Frequency	50 to 60 Hz
Input Frequency	50 to 60 Hz


Power Consumption	4 W
Lamp Current (Nom)	33 mA
Wattage Equivalent	40 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.4
Voltage (Nom)	220-240 V
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb Finish	Clear
Bulb Shape	A60 [A 60mm]
Approval and Application	
Energy Saving Product	Yes
Suitable For Accent Lighting	No
Energy Consumption kWh/1000 h	4 kWh

# Classic filament LEDbulbs

EyeComfort	Yes
<b>Product Data</b>	
Order product name	CLA LEDBulb ND 4-40W A60 E27 827 CL
Full product name	CLA LEDBulb ND 4-40W A60 E27 827 CL
Full product code	871869657399000
Order code	929001237102


Material Nr. (12NC)	929001237102
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696573990
Numerator - Packs per outer box	10
EAN/UPC - Case	8718696574003

## Dimensional drawing




Product	D	C
CLA LEDBulb ND 4-40W A60 E27 827 CL	60 mm	104 mm

## Photometric data



### Spectral Power Distribution Colour - CLA LEDBulb ND 4-40W A60 E27 827 CL

### General uniform lighting - CLA LEDBulb ND 4-40W A60 E27 827 CL



### Light Distribution Diagram - CLA LEDBulb ND 4-40W A60 E27 827 CL

## Classic filament LEDbulbs

