



# PAR30/PAR20 LED

## LEDspot 70W PAR30S 827 100-277V 25D ND

Philips PAR30S LED Single Optic Lamps with AirFlux Technology provide superior lighting aesthetics and optimal thermal efficiency in a sleek, lightweight design.


### Product data

General Information		Warm-up time to 60% light	
Cap-Base	E27 [E27]		0.5 s
Nominal lifetime	25,000 hour(s)	Power Factor (Fraction)	0.85
Switching Cycle	25,000	Voltage (Nom)	100-277 V
Lighting Technology	LED	Temperature	
EU RoHS compliant	Yes	T-Case Maximum (Nom)	80 °C
Light Technical		Controls and Dimming	
Color Code	827 [CCT of 2700K]	Dimmable	No
Beam Angle (Nom)	25 degree(s)	Mechanical and Housing	
Luminous Flux	900 lm	Bulb Shape	PAR30S [PAR 3.75 inch/95mm Short]
Luminous Intensity (Nom)	3,300 cd	Approval and Application	
Color Designation	Warm White (WW)	Suitable For Accent Lighting	Yes
Correlated Color Temperature (Nom)	2700 K	Energy Consumption kWh/1000 h	- kWh
Luminous Efficacy (rated) (Nom)	100.00 lm/W	Product Data	
Color Consistency	<6	Order product name	LEDspot 70W PAR30S 827 100-277V 25D ND
Color rendering index (CRI)	80	Full product name	LEDspot 70W PAR30S 827 100-277V 25D ND
LLMF At End Of Nominal Lifetime (Nom)	70 %	Full product code	871869674144300
Operating and Electrical		Order code	929001389612
Line Frequency	50 to 60 Hz	Material Nr. (12NC)	929001389612
Input Frequency	50 to 60 Hz	Numerator - Quantity Per Pack	1
Power Consumption	9 W	EAN/UPC - Product/Case	8718696741443
Wattage Equivalent	70 W		
Starting Time (Nom)	0.5 s		

# PAR30/PAR20 LED



Numerator - Packs per outer box	6
EAN/UPC - Case	8718696741450

## Dimensional drawing




Product	D	C
LEDspot 70W PAR30S 827 100-277V 25D ND	93 mm	91 mm

## Photometric data



Light Distribution Diagram - LEDspot 70W PAR30S 827 100-277V 25D ND



Spectral Power Distribution Colour - LEDspot 70W PAR30S 827 100-277V 25D ND



Accent Lighting Spots - LEDspot 70W PAR30S 827 100-277V 25D ND

# PAR30/PAR20 LED

## Lifetime



Lumen Maintenance Diagram - LEDspot 70W PAR30S 827 100-277V 25D ND

Life Expectancy Diagram - LEDspot 70W PAR30S 827 100-277V 25D ND

