



T8

16.9T8/MAS/48-840/MF25/P 10/1

Our TLEDs are available in InstantFit (Type A / Type C) or MainsFit (Ballast bypass / Type B) versions. The InstantFit lamps work on a broad variety of ballasts and LED drivers. Only InstantFit has over 15,000 lamp & ballast combinations delivering even light output, energy savings and a long lifetime. Our MainsFit products feature a double-ended design, simplifying installation while a proprietary safety circuit minimizes a shock risk. Lamp sizes range from 2-foot to 8-foot and U-bend with a variety of lumen outputs.

Product data


General Information		Input Frequency	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]	Input Frequency	50 to 60 Hz
Nominal lifetime	70,000 hour(s)	Power Consumption	16.9 W
Switching Cycle	50,000	Lamp Current (Max)	150 mA
Lighting Technology	LED	Lamp Current (Min)	65 mA
EU RoHS compliant	Yes	Wattage Equivalent	32 W
Light Technical		Starting Time (Nom)	0.5 s
Color Code	840 [CCT of 4000K]	Warm-up time to 60% light	0.5 s
Beam Angle (Nom)	180 degree(s)	Power Factor (Fraction)	0.9
Luminous Flux	2,500 lm	Voltage (Nom)	120-277 V
Color Designation	Cool White (CW)	UL Type	Type B - bypass the ballast
Correlated Color Temperature (Nom)	4000 K	Temperature	
Luminous Efficacy (rated) (Nom)	147.00 lm/W	Ambient temperature range	-4 °F to 113 °F
Color Consistency	<6	T-Case Maximum (Nom)	158 °F
Color rendering index (CRI)	80	Controls and Dimming	
LLMF At End Of Nominal Lifetime (Nom)	70 %	Dimmable	No
Operating and Electrical		Mechanical and Housing	
Line Frequency	50 to 60 Hz	Bulb Finish	Frosted

T8

Bulb Material	Glass
Product Length	47-1/4 inch
Bulb Shape	Tube, double-ended
Approval and Application	
Energy Saving Product	Yes
Approval Marks	RoHS compliance UL certificate DLC compliance
Product Data	
Order product name	16.9T8/MAS/48-840/MF25/P 10/1



Full product name	16.9T8/MAS/48-840/MF25/P 10/1
Order code	561712
Material Nr. (12NC)	929002439504
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677561710
Numerator - Packs per outer box	10
EAN/UPC - Case	50046677561715

Dimensional drawing



Product	D1	D2	A1	A2	A3
16.9T8/MAS/48-840/MF25/P 10/1	1-1/16 inch	1-1/8 inch	47-3/16 inch	47-1/2 inch	47-3/4 inch


Photometric data



Spectral Power Distribution Colour - 16.9T8/MAS/48-840/MF25/P 10/1


General uniform lighting - 16.9T8/MAS/48-840/MF25/P 10/1

Photometric data




Light Distribution Diagram - 16.9T8/MAS/48-840/MF25/P 10/1


Lifetime




Lumen Maintenance Diagram - 16.9T8/MAS/48-840/MF25/P 10/1



Life Expectancy Diagram - 16.9T8/MAS/48-840/MF25/P 10/1




Life Expectancy Diagram - 16.9T8/MAS/48-840/MF25/P 10/1



Life Expectancy Diagram - 16.9T8/MAS/48-840/MF25/P 10/1

T8

Lifetime



Lumen Maintenance Diagram - 16.9T8/MAS/48-840/MF25/P 10/1

