



Energy Saver Twisters

EL/dT 42W 3K 6/1

Looking for an energy saver that does not look like one? The Philips EnergySaver family provides energy efficient lighting options that don't just provide similar light as your standard incandescent light bulb, they also have the same classic shapes. Try the Philips EnergySavers and see how they truly provide advanced lighting designed around your needs.

Warnings and Safety

- Breaking a lamp is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a closed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- Compact fluorescent lamps have to be treated as special waste, they must be taken to your local waste facilities for recycling. The European Lighting Industry has set up an infrastructure, capable of recycling mercury, other metals, glass etc.

Product data

General Information		Operating and Electrical	
Cap-Base	E26 [Single Contact Medium Screw]	Line Frequency	50 or 60 Hz
Switching Cycle	5,000	Input Frequency	50 or 60 Hz
Rated Lifetime (Hours)	8,000 hour(s)	Power Consumption	42 W
Lighting Technology	Compact Fluorescent Integrated	Lamp Current (Nom)	610 mA
		Power Factor (Fraction)	0.55
		Voltage (Nom)	110-127 V
Light Technical		Controls and Dimming	
Color Code	830 [CCT of 3000K]	Dimmable	No
Color Designation	White (WH)		
Chromaticity Coordinate X (Nom)	440		
Chromaticity Coordinate Y (Nom)	403		
Correlated Color Temperature (Nom)	3000 K		
Luminous Efficacy (rated) (Nom)	70 lm/W		
		Mechanical and Housing	
		Bulb Shape	EL/DT

Energy Saver Twisters

Approval and Application

Mercury (Hg) Content (Nom) 2.7 mg

Product Data

Order product name EL/dT 42W 3K 6/1

Full product name EL/dT 42W 3K 6/1

Order code 427526

Material Nr. (12NC) 929689490101


Numerator - Quantity Per Pack 1

EAN/UPC - Product/Case 046677427528

Numerator - Packs per outer box 6

EAN/UPC - Case 50046677427523

Dimensional drawing



Product	D (max)	C (max)	F (max)
EL/dT 42W 3K 6/1	72.0 mm	176.8 mm	64.4 mm

