



TunnelView LED Large (TULL)

TunnelView Large 160LED 2700K 80CRI Counter beam

TunnelView Large 160LED 2700K 80CRI Counter beam - 99.7 lm/W

Lumec TunnelView tunnel/underpass luminaires provide seamless replacement of existing HID luminaires. This fixture is available in three sizes, offers multiple lumen packages, and a complete array of optical distributions, making it an outstanding solution for all types of tunnel and underpass applications. Includes Service Tag, Signify's innovative way to provide assistance throughout the life of the product.

Product data

General Information		Vibration Rating	
Service tag	Yes	Vibration Rating	Complies with ANSI C136.31, 3G
Lamp Source Code	LED	Initial Performance (IEC Compliant)	
Colour Temperature	2700 K	Luminaire Lumens	25874
CRI	80	Efficacy	99.7 lm/W
Photometric Distribution Type	Asymmetric	Product Data	
Mounting	Surface Pole Top Pole Arm	Order product name	TunnelView Large 160LED 2700K 80CRI Counter beam
Operating and Electrical		Order code	TULL-160L530-827-G1-CBL
Voltages	120/208/240/277/347/480/UNIV V	Material Nr. (12NC)	SC-7471663
Luminaire Input Watts	260	Catalog Number	TULL-160L530-827-G1-CBL
Approval and Application		Catalog Number Description	TunnelView Large 160LED 2700K 80CRI Counter beam
IP Rating	IP66		