



# TunnelView LED Large (TULL)

## TunnelView Large 128LED 3000K 70CRI Counter beam

TunnelView Large 128LED 3000K 70CRI Counter beam - 105.8 lm/W

Lumec TunnelView tunnel/underpass luminaires provide seamless replacement of existing HID luminaires. This fixture is available in three sizes, offers multiple lumen packages, and a complete array of optical distributions, making it an outstanding solution for all types of tunnel and underpass applications. Includes Service Tag, Signify's innovative way to provide assistance throughout the life of the product.

### Product data

General Information	
Service tag	Yes
Lamp Source Code	LED
Colour Temperature	3000 K
CRI	70
Photometric Distribution Type	Asymmetric
Mounting	Surface Pole Top Pole Arm
Operating and Electrical	
Voltages	120/208/240/277/347/480/UNIV V
Luminaire Input Watts	364
Approval and Application	
IP Rating	IP66

Vibration Rating	Complies with ANSI C136.31, 3G
Initial Performance (IEC Compliant)	
Luminaire Lumens	38560
Efficacy	105.8 lm/W
Product Data	
Order product name	TunnelView Large 128LED 3000K 70CRI Counter beam
Order code	TULL-128L900-730-G1-CBL
Material Nr. (12NC)	SC-7471673
Catalog Number	TULL-128L900-730-G1-CBL
Catalog Number Description	TunnelView Large 128LED 3000K 70CRI Counter beam